## GRAPHTEC

# Thermal Arraycorders WR300 SERIES



# **WR310:** High-end model with long-term analog data recording and large capacity data capture capabilities

Ideal for use in all kinds of research and development, as well as for control applications at production and manufacturing sites, quality control, and more

- Up to 1 MS/s sample rate on all channels
- Bandwidth (frequency response): DC to 200 kHz (using the WR3-V amplifier)

GRAPHTEC

### Thermal Arraycorders VVR300 SERIES


WR310-8/310-16

### **WR300**: Recorder designed specifically for long-term waveform recording

- Selection of models with 4, 8, or 16 input channels
- 50 mm/s chart speed
- 100 mm recording width for 4-ch models;
- 200 mm recording width for 8-ch and 16-ch models



WR300-8/-16



WR300-4

### Data Capture (Large capacity) — 40 GB HDD / PCMCIA card

Long-term data capture is possible with WR300 series at high speed. WR310 enables continuous measurement for 200 minutes at 10kS/s for 8-ch. 1 Mword/ch internal memory is standard.

#### Measurement data capture times

				(··	inon mode	anng on o	ornear interior)	
	1 μs	10 µs	100 µs	1 ms	5 ms	10 ms	100 ms	1 s
1 Mword/ch memory	1 s	10 s	1.6 min	16.6 min	1.4 h	2.8 h	28 h	11 days
HDD (1 file = 2 GB)*	2.08 min	20.8 min	3.4 h	1.4 days	7.2 days	14 days	144 days	1446 days
PCMCIA card (256 MB)					22 h	1.8 days	18.5 days	185 days
*One data capture operation is up to 2 GB								

### Recording (Thermal recording) — Various chart types/sizes are supported

Built-in 200 mm (8") wide thermal array printer in the 8- and 16-ch models; 100 mm wide printer in the 4-ch model.



### *Multi-function input* — Plug-in amplifiers

Models available with 4, 8 or 16 input channels. Plug-in 2-channel WR300 series amplifiers adapt the system to a wide variety of input types and sensors.




Synchronize your WR310 recordinas to IRIG-B time!

## Performance, reliability and ease of use.

### Display (8.4" color LCD monitor) — Easy operation and highly visible display

8.4" color LCD monitor for data display and graphical user interface.



### PC connection & remote interface





Includes Windows<sup>™</sup> software for setup, control, data transfer



Name	Function	Remarks
START/STOP	Measurement START/STOP	Input: CMOS type
(Level operation)	Pulse width: At least I s , Repeat cycle: At least 1 s	(0/+5V)
START/STOP	Measurement START/STOP	
(Edge operation)	Measurement starts and stops repeatedly whenever the L level is reached.	
	Pulse width: At least I s , Repeat cycle: At least 1 s	
EXT. FEED	Chart feed	
	Amount fed per pulse: 0.03125 mm , Max. high frequency: 660 pps (20 mm/s)	
EXT. TRIGGER	Trigger activation	
	L level pulse width: At least 10 ms	
EXT. SAMPLE	Data capture cycle	
	Pulse width: At least 500 ns , Repeat cycle: At least 10 µs	
TRIGGER	Trigger output	Output: CMOS type
Output	A CMOS type "L" pulse signal is output whenever a trigger is activated.	(0/+5V)
	Output pulse: At least 10 ms	

#### **WR300 Series Model Configuration Chart**

	WR300			WR310	
No. of channels	4	8	16	8	16
100 mm roll paper	Yes	No	No	No	No
100 mm Z-fold paper (for internal use)	Opt.	No	No	No	No
100 mm internal Z-fold unit	Opt.	No	No	No	No.
200 mm roll paper	No	Yes	Yes	Yes	Yes
200 mm Z-fold paper (for internal use)	No	Opt.	Opt.	Opt.	Opt.
200 mm internal Z-fold unit	No	Opt.	Opt.	Opt.	Opt.
200 mm Z-fold paper (long-length)	No	Opt.	Opt.	Opt.	Opt.
Long length 200 mm Z-fold unit	No	Opt.	Opt.	Opt.	Opt.
Logic amp	4-ch	8-ch	16-ch	8-ch	16-ch
IRIG	No	No	No	Yes	Yes
40 GB hard disk	No	No	No	Yes	Yes

#### **Basic Specifications**

Fu

#### **Main Unit Specifications**

Item	Details
Analog input	4-ch model: 2 slots, 8-ch model: 4 slots,
	16-ch model: 8 slots (amplifiers can be mixed in any combination)
Logic input	4-ch model: 4 channels, 8-ch model: 8 channels, 16-ch model: 16 channels
PC interface	Ethernet, USB 1.1
Memory capacity	1 Mword per channel
Internal memory	40 GB 2.5 inch hard disk*1, PCMCIA slot (Type II)
Isolation voltage	Between the AC power supply and casing: 1 minute at 1,500 V AC
Insulation resistance	Between the AC power supply and casing: 20 M $\Omega$ at 500 V DC
Backup functions	Setting conditions: EEPROM, Clock: Lithium batteries
Operating environment	0°C to 40°C, 30% to 80% RH (5°C to 35°C when using hard disk or printer)
Operating noise levels	Standby: 60 dBA max.
Rated power supply	100 to 120 V AC/200 to 240 V AC, 50/60 Hz
	(automatically selected for the voltage being used)
Power consumption	4-channel model: approx. 100 VA, 8-ch model: approx. 120 VA, 16-channel
	model: approx. 140 VA (when the print density is 50% and the printer is
	being used)
External dimensions	380 mm (W) x 296 mm (D) x 125 mm (H), (excluding rubber feet and
(approximate)	protrusions) [15W x 11.6D x 4.9H inches]
Weight (approximate)	4-ch model: 5.6 kg (including 2 amplifiers, less options) [12.32 lb.]
	8-ch model: 6.1 kg (including 4 amplifiers, less options) [13.4 lb.]
	16-ch model: 6.8 kg (including 8 amplifiers, less options) [15 lb.]
*1: WP210 only	

#### \*1: WR310 only

#### **Monitor and Printer Specifications**

	Item	Details		
Display screen 8.4inch (diag.) color TFT LCD		8.4inch (diag.) color TFT LCD		
D	isplay details	Setting windows, mode measurement values		
Thermal printer 4-ch model: 100 mm wide, 8 dots per mm				
		8-ch/16-ch models: 200 mm wide, 8 dots per mm		
Ν	leasurement mode	Recorder mode, FFT mode		
_	Display format	Display format: Y-T		
		Display direction: Horizontal scroll		
		No. of display zones: Zone specification, fixed format		
	Digital display	Digital display of measured values for up to 8 channels on right-hand side		
	· · ·	of screen		
	Display method	Scroll, Fixed		
	Print details	Waveforms and screen copy		
	Chart speed	1, 2, 2.5, 5, 10, 20, 25, 50 mm/s		
	·	1, 2, 2.5, 5, 10, 20, 25, 50, 100 mm/min, mm/h		
	Printing accuracy	Y: ±0.3% ±1 dot, T: ±2% ±0.5 mm		
	Annotation printing	System annotation: (System, User, System & User, OFF)		
ge		Channel annotation: (Amp, User, Amp & User, Value, OFF)		
mode	No. of annotation characters	10 to 32 characters		
je	Annotation printing interval	10 cm to 100 cm in 10 cm steps		
Hecorder	Captured data replay	Waveform display/scroll, Waveform zoom-in/zoom-out, Cursor function,		
ĕ		Calculation function, Data search function		
	Waveform expansion/	Time axis fixed zoom-in/zoom-out: x 10 to x 1/1000 (data between		
		specified cursors)		
	Compression functions	Time axis variable zoom-in/zoom-out: data between specified cursors		
		Voltage axis variable zoom-in/zoom-out: data between specified cursors		
	Cursor functions	Cursor readout function/Scroll function/Zoom function		
	Calculation functions	Arithmetic operations/Moving average/Log/Index mean/Absolute		
		value/Differential and integral (two types of integral)/Second differential		
		(two types of second integral)/Sine/Cosine/Tangent/Arcsine/Arccosine		
		/Arctangent/Pi (π)		
	Data search	Date/Time: Data search from specified time/date		
		Level: Data search above (below) specified level		
	Analysis functions	Auto-correlation: Linear spectrum, power spectrum, power spectrum		
		density, RMS spectrum		
		Cross-correlation: Cross spectrum, transfer function, coherence function		
	Analysis frequencies	400 kHz, 200 kHz, 100 kHz, 80 kHz, 40 kHz, 20 kHz, 10 kHz, 8 kHz,5 kHz,		
_		4 kHz, 2 kHz, 1 kHz, 800 Hz, 500 Hz, 400 Hz, 200 Hz, 100 Hz, 80 Hz,		
mode		40 Hz, 20 Hz, 10 Hz, 8 Hz, 5 Hz, 4 Hz, 2 Hz, 1 Hz, 0.8 Hz, 0.5 Hz, 0.4 Hz,		
Ĕ		0.2 Hz, 0.1 Hz, 0.08 Hz		
Ŧ	Number of analysis channels	4 ch		
	Window functions	Hanning & rectangular windows		
	Number of sampling points	1,000 points, 2,000 points		
	Averaging	Summation, exponential, peak hold		
	Display format	1 Division, 2 Divisions, 4 Divisions, Nyquist		
	Print details	Screen copy		

#### Data Capture Function Specifications

unction	n Item		Details
	Captured data		Measurement conditions, measurement data
	Capture capacity	Memory	1 Mword per channel
		PCMCIA card	Depends on usage conditions
Internal capture		Hard disk*1	40 GB (1 file: 2 GB max.)
apt	Sampling interval	Memory	Depends on amplifier
alc		PCMCIA card	Max. 5 ms
eru		Hard disk*1	8 ch data capture : Max. 1 $\mu s,$ 16 ch data capture: Max. 2 $\mu s$
<u>I</u>			Note: 10 µs for temperature ranges
	Memory banks	(Block) *2	1, 2, 4, 8, 16, 32, 64, 128
	Capture start specification		After a trigger, capture starts simultaneously with waveform
			recording (selectable On/Off)
	Captured data		Measurement conditions, measurement data
	Capture capac	ity	Depends on PC connected
ture	Sampling inter	val	Depends on amplifier
cap	Transfer data	During measurement	Min/Max values transferred in real-time
ž	details	After measurement	Data captured to memory/hard disk
TX0	Sampling interval Transfer data During measurement details After measurement Data backup*2		Memory, PCM-CIA card, hard disk (data capture capacity and
Se			sampling interval are the same as for Internal capture).
	Capture start s	pecification	After a trigger, capture starts simultaneously with waveform
			recording (can be set On/Off)

\*1: WR310 only \*2: When using memory

#### **Trigger Specifications**

Item	Details		
Time gate	OFF, Relative time, Absolute time		
Action	Single, Repeat		
[Start condition] source	OFF: Start trigger via pressing the START key		
	Internal: Start trigger via AND/OR combination of measured signals		
	Manual: Start trigger via pressing the TRIGGER key		
	External: Start trigger via TRIGGER IN signal on remote connector		
[Stop condition] source	OFF: Stop trigger via pressing the STOP key		
	Internal: Stop trigger via a combination of measured signals		
	Manual: Stop trigger via pressing the TRIGGER key		
	External: Stop trigger via TRIGGER IN signal on remote connector		
	Time: Stops measurement at preset time		
Combination	Level OR, Level AND, Edge OR, Edge AND		
Judgment mode	Edge: Rise time (↑), Fall time (↓) Level: H (High), L (Low)		
	Window: IN, OUT, OFF		
Level	-100% to +100% of setting range in 1% steps		
Trigger Counter (when the	Number of times: 1 to 255		
Combination setting is Level)	Filter: Product of the Sampling Interval and the Number of Times settings		
	(can only be set when the Function setting is Memory).		
Pretrigger	Internal memory: 0% to 100% in 1% steps		
	PCMCIA card, HDD: On/Off		
Logic trigger	Pattern: H (High), L (Low), X (Don't care)		
	Judgment mode: When the pattern is matched		

#### **Software Specifications**

Item	Details	
Compatible operating system	Windows 2000/XP	
Functions	Measurement conditions setting, data measurement, file conversion, report	
	creation (option)	
Measurement condition settings	WR300/310 control, communication conditions setting	
Measurement function	Recorder mode	
Display format	Y-T	
Display direction	Horizontal scroll	
No. of display zones	Zone specification	
Digital display	Digital display of measured values for up to 8 channels on left side of screen	
Display method	Scroll, fixed	
Captured data replay	Waveform display/scroll/waveform expansion/compression	
Cursor functions	Cursor readout, data search	
File conversion	TEXT, CSV, DADISP, GBD	
Report creation (option)	Report creation mode or waveform screen copy and paste	

#### **Standard Accessories**

Thermal paper (4ch PR230 100mm, 8ch-16ch PR231A 200mm)	1 roll
Roll paper bobbins	2
REMOTE connector	1
LCD Protector	1
User Guide CD-ROM with OPS023 Application Software, USB Driver	1
Quick Guide	2
AC cable (RSC-110)	1



#### WR3-V Amplifier (for voltage measurement)

Item	Details	
No. of channels	2 channels per module	
Input configuration	Independent, unbalanced input for each channel (floating ground)	
Input resistance	1 MΩ ±1%	
Input coupling	AC, DC, GND, CAL, (1/2 F.S.), OFF	
Measurement range	50, 100, 200, 500 mV/F.S.	
	1, 2, 5, 10, 20, 50, 100, 200 V/F.S.	
Input filters	Line: 1.5 Hz (-3 dB) at -6 dB/oct	
	Low-pass : 5 Hz, 10 Hz, 50 Hz, 500 Hz, 5 kHz, 50 kHz (-3 dB) at -6 dB/oct	
Accuracy (23±3°C)	±0.25% of F.S.	
Temperature coefficients	Zero point: 0.02% of F.S. /°C	
	Gain: 0.02% of F.S. /°C	
Insulation resistance	100 MΩ (at 500 V DC)	
Isolation voltage	Between input terminal and casing: 1 minute at 1000 VAC	
Permissible signal source resistance	Max. 1 kΩ	
A/D converter	Sampling interval: 1 µs	
	A/D resolution: 12-bit	
Common mode rejection ratio	80 dB (typ.) (50/60 Hz, Signal source resistance: max. 500Ω)	
Signal/noise ratio	-46 dB (typ.) 200(Vp-p at 50 mV range (with +/- shorted)	
Frequency response	DC coupling: DC to 200 kHz (+/-3 dB Typ.)	
	AC coupling: 10 Hz to 200 kHz (+1/-4.5 dB Typ.)	
Max permissible input voltage	Between +/- terminals: 5 V to 200 V range : 200 V DC (DC + AC <sub>P-P</sub> )	
	50 mV to 2 V range: 30 V DC (DC + AC <sub>P-P</sub> )	
	Between input terminals and GND: 33 V AC rms	
Input terminal type	BNC	



ltem	Details		
No. of channels	2 channels per module		
Input configuration	Independent, unbalanced input for each channel (floating ground)		
Input resistance	1 MΩ ±1% constant		
Input coupling	AC, DC, TEMP., GND, CAL (1/2 F.S.), OFF		
Measurement range	[Voltage] 20, 50, 100, 200, 500 mV		
	1, 2, 5, 10, 20, 50, 100, 200, 500 V		
	Auto		
	[Temperature] TC-K: -200 to 1300 °C		
	TC-J: -200 to 1100 °C		
	TC-T: -200 to 400 °C		
	TC-R: 0 to 1600 °C		
	TC-E: -200 to 800 °C		
	TC-B: 600 to 1700 °C		
Input filters	[Line] 1.5 Hz (-3 dB) at -6 dB/oct.		
	[Low-pass] 5, 10, 30, 50, 500Hz, 5 kHz (-3 dB) at -6 dB/oct.		
Accuracy (23°C ±3 °C)	[Voltage] ±0.25% of F.S.		
(Temperature accuracy	[Temperature] < TC-K, J, E >		
includes reference contact	-200 °C to 0 °C: ± (1% of rdg + 3.5 °C)		
compensation accuracy)	Other: ± (0.2% of rdg + 3.5 °C)		
	< TC-T>		
	−200 °C to 0 °C : ± (0.8% of rdg + 3 °C)		
	Other: ± (0.2% of rdg + 3 °C)		
	< TC-B >		
	0 °C to 200 °C: ± 9.5 °C		
	200 °C to 800 °C; ± 6.5 °C		
	Other: ±(0.2% of rdg + 4.5 °C)		
	<tc-b></tc-b>		
	600 °C to 700 °C: ± 9.5 °C		
	Other: ± (0.2% of rdg + 5.5 °C)		
Temperature coefficient	Zero point: 0.01% of F.S./ °C		
remperature coemcient	Gain: 0.02% of F.S./ °C		
Insulation resistance	100 MΩ (at 500 V DC)		
Isolation voltage	Between input terminal and casing: 1 minute at 1,000 V AC		
Permissible signal source resistance	Max. 1 k $\Omega$		
Input bias current	2nA (typ.)		
A/D converter	Sampling interval: 10 µs		
A/D converter			
Common mode rejection ratio	A/D resolution: 16 bits (out of which 14 are internally acknowledged)		
,	100 dB typ (120 dB with Line Filter on)		
Signal/noise ratio	-46 dB (typ) 100 μVP-P at 20 mV range (with +/- shorted) DC coupling: DC to 20 kHz (+1/- 3 dB Typ.)		
Frequency response			
Manual and the family of	AC coupling: 10 Hz to 20 kHz (+1/- 4.5 dB Typ.)		
Max permissible input voltage	Between +/- terminals: 2 V to 500 V range : 500 V DC (DC + $AC_{p,p}$ )		
	20 mV to 1 V range: 100 V DC (DC + $AC_{P,P}$ )		
	Between input terminals and GND: 33 V AC rms		
Input terminal type	Banana connector (two connectors)		



#### WR3-DCB Amplifier (for strain measurement)

Item	1	Details	
No. of channels		2 channels per module	
Input terminals/format		Independent balanced input for each channel (NDIS strain input connectors)	
Input coupling		DC, CAL+, CAL-, ZERO, OFF	
Measurement range		Voltage: 1000 to 20,000 x 10 <sup>-6</sup> strain FS (1/2/5 steps)	
Max permissible input	Differential input	10 VDC (DC+ACp-p)	
	Sync voltage	100 VACrms	
Insulation resistance		Min. 100 MΩ (at 500 V DC)	
Isolation voltage		Between input terminal and casing: 1 minute at 1,000 V AC	
A/D converter		Sampling interval: 10 µs	
		Resolution: 16-bit (14-bit effectively)	
Common mode reject	on ratio	80 dB typ (50/60 Hz)	
Signal/noise ratio		Max. 50 x 10 <sup>-6</sup> strain (2 V DC, 350 Ω)	
Input resistance		Approx. 10 MΩ (5 M + 5 M)	
Accuracy (23 °C ±3 °C	2)	±(0.3% of F.S. +1.2 x 10 <sup>-6</sup> strain)	
Frequency bandwidth		DC to 20 kHz (+1/-3 dB)	
Stability	Zero point	±1.2 x 10 <sup>-6</sup> strain/ °C	
		±10 x 10 <sup>-6</sup> strain/8 h	
		$\pm 10 \ x \ 10^{-6}$ strain/0.5 h (initial drift / from 10 s after power on)	
	Gain	±0.02% of F.S./ °C	
		0.10% of F.S./8h	
Filters	Line	1.5 Hz (+1/-3 dB) at -6 dB/Q (octave)	
	L.P.F	10 Hz, 30 Hz, 100 Hz, 300 Hz, 1 kHz (-3dB) at -12 dB/oct	
Gage ratio		2.0 fixed	
Gage resistance		120 to 1000 Ω	
Bridge voltage	Voltage	DC 2 V	
	Accuracy	±0.2%	
	Stability	±0.01%/ °C	
Balance adjustment	Method	Auto balance adjustment method	
	Accuracy	±10 x 10 <sup>-6</sup> strain ( <sup>-6</sup> = microstrain)	
	Range	Resistance ±2% (10,000 x 10 <sup>-6</sup> strain)	

#### WR3-FV Amplifier (for frequency measurement)

Item		Details				
Input terminals/format		Independent unbalanced input for each channel (floating ground)				
Input coupling		DC (0 V reference), OC (+2.5 V reference), OFF				
Measurement range		200 Hz to 40 kHz F.S. (1/2/4/5 steps)				
Max permissible	Between +/- terminals	DC 60 V (DC+ACp-p)				
input	Between floating terminals	30 VACrms				
A/D converter		Sampling interval: 4 µs (250 kHz)				
		Resolution : 12 bits (out of which 14 are internally acknowledged)				
Input resistance		DC: Approx. 100 k Ω				
		OC: Approx. 10 k Ω				
Accuracy		±0.5% of F.S.				
Max. input frequency		40 kHz				
Min pulse width		Min. 2.5 μs				
Min. voltage		Min. ±1 V relative to the reference value				
Low-pass filters		100 Hz, 1 kHz, 10 kHz (-3 dB) at -6 dB/oct				



#### Logic Amplifier (for measurement of logic signals)

Item	Details		
No. of channels	4-ch model: (4 channels/logic input terminal x 1)		
	8-ch model: (8 channels/logic input terminal x 2)		
	16-ch model: (16 channels/logic input terminal x 4)		
Input voltage range	0 to 25 V max. (single ground input)		
Threshold level	TTL (+1.4 V), CMOS (+2.5 V), Contact (+5.0 V)		
Sampling interval	1 µs max. (regardless of which analog amplifiers are installed)		
Trigger setting	8-channel pattern trigger		
Display/Recording	On/Off switchable for each group (1 group: 4 channels)		
Display/Record position specification	Display/Recording position can be specified for each group in each zone		

0

#### IRIG (Time Code) (WR310 only)

Item	Details		
Input signal type	Modulated, demodulated		
Output signal type	Demodulated		
Input signal format	IRIG-B, IRIG-E		
Print record	System annotation printing		
Display Asterisk mark [*] displayed when time code received			
	When a time code has not been received, the recorder's internal time is displayed		
	The year displayed is the internal function clock		
Input connector	BNC		

#### Options/Accessories/Supplies Charts

#### Units

Unit	Model No.	Details	
Voltage measurement amplifier	WR3-V AMP	Can be added later	
Voltage/temperature measurement amplifier	WR3-M AMP	Can be added later	
DC strain measurement amplifier	WR3-DCB AMP	Can be added later	
Frequency measurement amplifier	WR3-FV AMP	Can be added later	
200 mm long-length Z-fold unit	B-522	Can be added later	
100 mm internal Z-fold unit	B-523	Can be added later	
200 mm internal Z-fold unit	B-524	Can be added later	


#### Accessories

Accessories	Model No.	Details		
Input cable (8-cable set)	B-331	2-pin cable (banana terminal) bare tips		
Input cable (16-cable set)	B-335	2-pin cable (banana terminal) bare tips		
Clamp adapter (1200 A)	CM-102			
Digital clamp meter	CM-111			
Logic amplifier probe	RIC-07			
Alligator clip cable	RIC-08			
IC clip cable	RIC-09			
Probe set (Set RIC-07 to 09)	RIC-10			
Floating voltage input probe	CM-105			
Voltage conversion probe	CM-106			
Clamp meter temperature probe	RIC-110			
Line separator	CM-108			
Safety adapter	SMA-102	High-voltage BNC-to-banana		
		conversion adapter		

#### **Supplies**

Supplies	Model No.	Min. Qty.	Details
Roll paper (thermal recording paper)	PR230	5 rolls	100 mm wide, 40 m length
Z-fold paper (thermal recording paper)	PZ230	5 packs	100 mm wide, 40 m length
Roll paper (thermal recording paper)	PR231A	10 rolls	200 mm wide, 40 m length
Z-fold paper (thermal recording paper)	PZ233	5 packs	200 mm wide, 40 m length
Z-fold paper (thermal recording paper)	PZ231A	5 packs	200 mm wide, 100 m length
Head cleaner	B-368	1 set	For cleaning the thermal recording head

#### **External Dimensions**



Brand names and product names listed in this brochure are the trademarks or registered trademarks of their respective owners. Specifications are subject to change without notice.



Tel Toll Free: 800.854.8385 Fax: 949.855.0895

(				
	ΛI		h	si
	///	e	L	5

http://www.graphtecamerica.com